



Water Emulsion Device ISO TS 16332

FOR TESTING DIESEL FUEL FILTER WATER SEPARATION EFFICIENCY

Produces water droplet size distributions found in real diesel fuel systems (i.e. pressure and suction filters). Dedicated to the new up-to-date diesel fuel filters water removal efficiency test procedure ISO TS 16332 Annex A.



Orifice plates




Aperture Housing

TECHNICAL DATA

- ♦ Flow rate from 50 to 900 L/h
- ♦ Water content from 0.15 to 2%
- ♦ Water droplet size from 10 to 600 µm
- ♦ In Duralumin with anti oxidation treatment, standard Connection size 3/8" BSP
- ♦ Free: 5 extra aperture plates


www.ifts-usa.com

IN LINE APERTURE HOUSING



Connect the aperture housing on a flexible line with Teflon tape. Unscrew 3 or 4 times. Put the plate from the base of orifice housing. Screw on. Connect pressure lines.

ORIFICE PLATE



Orifice size is printed the external face



SPARE PARTS

- Orifice Plates: 2 unmarked; 3 marked

IFTs Inc., USA
 200 Pond Avenue
 Middlesex, NJ 08846
 USA
 Tel: (732)-629-7548
 Fax: (732)-629-7556
 Email: info@ifts-usa.com
 http://www.ifts-usa.com